

Workers, safety managers and new regulations all demand an added level of protection when working with shared items, equipment, or contact surfaces. Gloves are now being relied upon as a new line of defense against contamination.

Introducing G-Tek® VR-X™

The FIRST reusable coated seamless knit glove offering Advanced Barrier Protection using patent-pending glove technology found only in G-Tek® VR-X™ series gloves.

NEW RISKS REQUIRE INVENTIVE SOLUTIONS

WHAT IS ADVANCED BARRIER PROTECTION?

PIP®, in collaboration with its key partners, has developed a new polyurethane-based coating that offer unprecedented barrier protection in a work glove.

TESTED TO PERFORM IN A WORLD OF NEW GLOBAL RISKS



BARRIER PROTECTION

> ISO 374-2:2019

> ISO 374-5:2016

Performance testing and terminology to determine protection against microorganisms risks



MICROORGANISM ACTIVITY

Polyurethane-based coating is tested in accordance to:

- > ISO 21702:2019
- >ISO 20743:2013

Specifies quantitative test methods to determine the antibacterial activity of all antibacterial textile products including nonwovens





SILICONE-FREE



TOUCHSCREEN COMPATIBLE




33-VRX180

' ISO 21702 This document specifies proper methods for measuring antiviral activity on plastics and other non-porous surfaces of antiviral-treated products against pecified viruses. Due to the individual sensitivities, the results of one test virus might not be applicable for other viruses.

** Test reports are available upon receipt of written request directly from customer inquiring



Disposable gloves are NOT an ideal, sustainable, or effective solution for worker confidence. Workers must wear gloves that help protect them from cuts and abrasion while providing barrier protection. Gloves need effective grip to help workers be productive. That's why they need G-Tek® VR-X™ gloves.







IDEAL FOR:

- > MANUFACTURING
- > CONSTRUCTION
- > MAINTENANCE & REPAIR
- > PRECISION ASSEMBLY
- > SHIPPING & PACKAGING
- > SMALL SHARP PARTS HANDLING
- > INSPECTION











16-VRX380

- Polyurethane coating provides a tactile grip in wet, dry and slightly oily conditions
- Ultra-lightweight 18-gauge PolyKor® blended yarn liner delivers cut resistance PLUS outstanding dexterity and tactile sensitivity for precision handling
- Touchscreen compatible reduces risk of cross-contamination
- Patent-pending glove technology
- Launderable offers significant cost savings and reduced environmental impact, especially when compared to disposable glove alternatives



IDEAL FOR:

- > MANUFACTURING
- > CONSTRUCTION
- > MAINTENANCE & REPAIR
- > PRECISION ASSEMBLY
- > SHIPPING & PACKAGING
- > SMALL PARTS HANDLING > INSPECTION
-







33-VRX180


- Polyurethane coating provides a tactile grip in wet, dry and slightly oily conditions
- Ultra-lightweight 18-gauge liner delivers outstanding dexterity and tactile sensitivity for precision handling
- Touchscreen compatible reduces risk of cross-contamination
- Patent-pending glove technology
- Launderable offers significant cost savings and reduced environmental impact, especially when compared to disposable glove alternativess


STYLE	ANSI CUT	EN388	EN374-5	COATING	COATING COVERAGE	COATING COLOR	LINER	LINER COLOR	CONSTRUCTION	GAUGE	SIZES	PROP 65
16-VRX380	A3	4X32C	Yes	Polyurethane	Full Hand	Black	PolyKor®	Black	Coated Seamless Knit	18	XS-2XL	<u></u> C
33-VRX180	-	3111X	Yes	Polyurethane	Full Hand	Black	Nylon	Blue	Coated Seamless Knit	18	XS-2XL	<u></u> C

C = ▲ WARNING: Cancer - www.P65Warnings.ca.gov

WARNING STATEMENT: G-Tek[®] VR-XTM gioves are for industrial use only. They are not for retail or consumer sale or use. G-Tek[®] VR-XTM meets the testing requirements as outlined in this brochure. These standards relate to performance of protective work gloves. This product has not been FDA delated or approved, it is not intended for use in any "clinical or frontline setting" nor does it infer to be PPE intended to prevent the spread of COVID-19. Gloves with enhanced barrier protection help prevent direct personal contact with tens, parts, equipment, or surfaces that may be shared. As outlined in the PIP® ESSENTIALSTM SafetyBook, we advise our customers to follow the CDC's recommendations regarding the primary method of helping prevent the spread of germs.

G-TEK® VR-X™ THE SUSTAINABLE CHOICE vs. DISPOSABLE NITRILE GLOVES







Annual numbers are based on the usage of 3,000 workers changing out four pairs of disposable nitrile gloves per day as opposed to 1 pair of G-Tek[®] VR-X[™] gloves every 5 days. Usage based on medium duty handling tasks.



PROTECTIVE INDUSTRIAL PRODUCTS, INC.

968 Albany Shaker Road | Latham, NY 12110 518-861-0133 | 800-262-5755 sales@pipusa.com | www.pipusa.com

