

# Product Information ISO Class 5 - 8 Cleanroom Class 100 - 100 00

Cleanroom Class 100 – 100,000 EU Grade A-D

# Pro-Wipe® 750

## Polypropylene / Cellulose Composite Nonwoven Cleanroom Wiper

Pro-Wipe® 750 is a thermally bonded multi-layer composite nonwoven wiper recommended for ISO Class 5 and above environments composed of a layer of cellulose bonded between two outer layers of

polypropylene. This combination of properties provides Pro-Wipe® 750 with exceptional cleanliness, absorbency and chemical resistance to strong solvents including acids



Other Class 5 and above nonwoven wipers

#### Key Attributes

- 60% polypropylene / 40% cellulose nonwoven
- Multi-layer composite with cellulose layer thermally bonded between the two polypropylene outer layers
- High loft and soft texture
- No binders or other chemical additives

#### Benefits

- Engineered for compatibility with acid solvents
- Extremely durable and pure with very low particle and fiber generation
- High absorbency to weight ratio may reduce cost in use compared to similar weight nonwovens
- Chemically compatible with common cleaning and disinfecting solutions
- Autoclavable

#### **Environmental**

- Complies with RoHS 2002/05 and REACH requirements
- High absorbency to weight ratio may reduce wiper usage and landfill waste pounds compared to similar weight nonwovens
- 40% cellulose fiber content is biodegradable

#### Applications

- Designed for use in ISO Class 5 and higher cleanroom environments
- Excellent choice for general spill pick up and cleaning surfaces
- Designed for removal of etchants, acids, and other chemical spills
- · Excellent for cleaning scratch sensitive surfaces
- Ideal for tray lining and other lab applications
- · General wiping in component prep, compounding and wash areas
- · Excellent for general wiping and cleaning in biomedical environments
- Certified for contact with food per EC Regulation 1935(2004)

#### Pre-Wetted Option

The same wiper material can be provided in pre-wetted formats for reduced VOC emissions, increased convenience, increased productivity, improved solvent control and cleaning protocol repeatability and reduced costs.

#### Sterile Validated Option

For aseptic processing areas, the same wiper material can be provided in a gamma irradiated validated sterile to a 10<sup>-6</sup> sterility assurance level. Dry and pre-wetted versions available.

BlueSorb® 750 Durx® 670

Durx® 770

MicroFirst<sup>®</sup>
MicroFirst LP<sup>®</sup>

ProjX® 700

Pro-Wipe® 880

ValuClean® Plus

#### www.berkshire.com Contact: Tel 1 800 242 7000 / 1 413 528 2602 info@berkshire.com

America	Tel 1 413 528 2602	Fax 1 413 528 2614	info@berkshire.com
Europe	Tel 44 (0) 870 757 2877	Fax 44 (0) 870 757 2878	enquiries@berkshire.uk.com
SE Asia	Tel 65 6252 4313	Fax 65 6252 4312	enquiries@berkshire.com.sg
Japan	Tel 81 3 5827 2380	Fax 81 3 5827 2382	master@berkshire.co.jp



#### **Technical Data:**

Attribute		Units	Value	Test Method	
Basis Weight		g/m²	69.4	TAPPI T-410	
Caliper		μm	337	TAPPI T-411	
Fibers	≥100µm	fibers/cm <sup>2</sup>	3.6	IEST-RP.CC004.3, Sec 6.1.3 / Sec 6.2.2	
Particles	≥0.5µm	x10³/cm²	8.5	IEST-RP.CC004.3, Sec 6.1.3 / Sec 6.2.1	
Sorbency	Capacity	mL/m²	471	IEST-RP.CC004.3, Sec 8.1 modified / Sec 8.2 modified	
	Efficiency	mL/g	6.8		
	Rate	seconds	1		
Non-Volatile Residue	DI Water	g/m²	0.094	IEST-RP.CC004.3, Sec 7.1.2	
	IPA	g/m²	0.046		
lons	Na <sup>+</sup>	ppm	79	IEST-RP.CC004.3, Sec 7.2.2	
	K <sup>+</sup>	ppm	15		
	Ca**	ppm	1.1		
	Mg <sup>++</sup>	ppm	0.25		
	CI-	ppm	48		

- Technical data represented in this table are typical values at the time of publication. These should not be used as product specifications.
- Due to differences in test methods applied and equipment utilized by different wiper manufacturers, valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions
- Third party testing can be performed upon request

#### **Order Information:**

Product	Number	Size	Shts/pk	Pks/cs	Style
Pro-Wipe® 750	PW750.0909.20	9x9" (23x23cm)	150	20	Stacked
Pro-Wipe® 750	PW750.1212.20	12x12" (30x30cm)	75	20	Stacked

For more information on our other contamination control products or technical consultation, please contact your Berkshire Sales Representative or e-mail: info@berkshire.com

### Other Berkshire products

For information on our other products, please click on the relevant text.



**Wipers** 



**Mop Systems** 



Face Masks



**Glove Liners** 



**Documentation Systems** 



Contact: Tel 1 800 242 7000 / 1 413 528 2602 / info@berkshire.com